

SubjectID	Sex	Age	Ear Canal L	Ear Canal R	Silicone Dome Size
			length in [mm]*		
ITA2	m	31	3,3	3,0	M
ITA3	f	28	2,8	2,8	S
ITA4	m	28	3,1	3,1	L
ITA5	m	60	3,2	3,5	M
ITA6	m	33	3,4	3,4	L
ITA7	f	25	3,0	3,0	S
AU05RD24	f	27	2,7	2,7	M
CH09US24	f	31	3,3	3,3	L
EK06AS04	m	34	3,1	3,0	L
EL08RD06	f	33	3,0	3,0	M
EN07NS03	f	21	3,0	3,0	S
ER03ED10	m	27	3,5	3,5	M
ER03IM11	m	28	3,5	3,5	L
ER04UT30	f	29	n.a.	n.a.	XS
ER05EN06	m	33	3,3	3,3	L
ER06PH18	m	27	3,2	3,1	L
ER07ED05	f	33	2,8	2,7	S
ER09US30	m	29	3,2	3,2	M
HM08CO04	m	33	3,2	3,2	L
IN04ER21	f	24	2,8	2,8	M
MI08LF31	m	28	3,0	2,6	M
NE06RG13	f	24	3,0	3,0	S
NK07ER02	m	32	n.a.	n.a.	M
OF05UD28	f	38	3,0	3,2	M
SZ08CH09	m	25	3,0	3,0	M
KEMAR					L

Ear canal length was determined by measuring the length of the probe tubes from the eardrum to the tragus