Nanosized copper-based catalyst for automotive: physicochemical characterization.

A. Soto Beobide¹, A. M. Moschovi², G. N. Mathioudakis¹, M. Kourtelesis², Z. G Lada¹, K. S. Andrikopoulos^{1,3}, L. Syggelou¹, V. Dracopoulos¹, I. Yakoumis², G.A. Voyiatzis¹



¹ Foundation for Research and Technology / Institute of Chemical Engineering Sciences FORTH/ICE-HT, Patras, Greece

²Monolithos Catalysts & Recycling Limited, Athens, Greece

³Department of Physics, University of Patras, Patras, Greece

* E-mail address of presenting author: asoto@iceht.forth.gr



Nanotechnology is conceived as a Key Enabling Technology, becoming an increasingly research area providing functional materials to many industrial sectors, such as automotive, health, packaging, textiles, construction, etc.

The main objective of **DIAGONAL** project is to increase the **understanding on Multi-Component NanoMaterials (MCNM) and High Aspect Ratio Nanoparticles (HARNS)** behavior along their life cycle from NM design and production to its application into Nano-Enabled products (NEP).

DIAGONAL aims to bring new methodologies to guarantee long-term nanosafety and contribute to fill current gaps in: Risk Assessment, Risk Management and Risk Governance.


DIAGONAL will bring **Safe-by-Design knowledge** and tools to a development stage which can be implemented **in the MCNM and HARNs related industries**, relying on experimental (in vitro) and modelling (in silico) research to understand and ultimately predict the interactions among the NM components, their transformation products, and between the NMs and the environment, promoting a better understanding of potential adverse effects on human health, and biota.



The case: Nanocatalytic powders as coating in automotive industry Cu/Pd/Rh doped on Ce/Zr mixed oxide

- In the automotive industry, catalytic devices accumulate concentrated loading of platinum group metals (PGMs, platinum, palladium, rhodium) as the active catalytic phase.
- The aim of **MONOLITHOS Catalysts Ltd** is the partial substitution of an amount of PGMs (mainly platinum) with abundant non-PGMs (transition metals). Several efforts have been made to use transition metals as substitutes and among them copper seems to be one of the best.

PROM100 "fresh": catalyst that has not been used at all **PROM100 "aged":** artificially aging by submitting to hydrothermal (10% water) heating at 1050 °C for 4h. EU Directives for simulating more than 60,000Km of mileage of a car.



Physico-chemical characterization of PROM100 catalyst and its transformation along life cycle


Definition of Nanomaterial According to Commission's recommendation [1]

Material with 50% or more of the particles in the number size distribution, present one or more external dimensions in the size range 1 nm-100 nm A material should be also considered nano when the specific surface area by volume of the material is >60 m²/cm³


A) Gas porosimetry


C) Raman Characterization


D) X-ray photoelectron spectroscopy, XPS



B) Scanning electron microscopy, SEM









Raman Shift, cm⁻¹

CeO₂cubic fluorite: intensity peak at 465 cm⁻¹


Ce_{1-x}Zr_xO₂ mixed oxides:







PROM100-fresh: $Ce_{0,75}Zr_{0,25}O_2$ PROM100-aged: CeO_2 , ZrO_2 Monoclinic($P2_1/c$), $Zr_{0.9}Ce_{0.1}O_2$ Tetragonal

E) X-ray diffraction, XRD





New peaks: ZrO₂ monoclinic phase [3]



340

330

320

Conclusions:

Artificially aged catalyst can not be considered as nano-material. (Gas porosity & SEM)
Catalyst PROM100-fresh present the Ce_{0.75}Zr_{0.25}O₂ mixed oxide. Artificial ageing produces partial phase separation and PROM100-aged is present mainly as CeO₂ and ZrO₂ monoclinic phases with a small contribution of ZrO₂ tetragonal phase. (Raman & XRD)
For PROM100-aged catalyst there is decrease of Pd and Copper is found mainly as Cu²⁺. (XPS)

ensity

Ţ

Relativ

REFERENCES:

[1]https://eur-lex.europa.eu/legal-content/EN/TXT/HTML/?uri=CELEX:32011H0696&from=EN

[2] S. Loridant et al. Raman spectroscopy as a powerful tool to characterize ceria-based catalysts. Catalysis Today, Elsevier, 2021, 373, 98-111.

[3] P. Barberis et al. On Raman spectroscopy of zirconium oxide films, Journal of Nuclear Materials, 1997, 246, 232-243.

360

350



This project has received funding from the European Union's Horizon 2020 research and innovation programme under grant agreement No 953152.